

定位襯套 · 帶有軸環，DIN 172 A EH 23112.




產品描述

定位或鑽孔襯套用於在同一位置鑽出重複孔，以確保重複性。
硬化和磨削定位襯套可用作鑽頭，軸等的耐磨導向。

材質


- 表面硬化鋼，表面硬化


圖面



訂單資訊

尺寸						定位孔	[g]	品號
d_1 F7	l_1	d_2 n6	d_3	l_2	r	D H7 [mm]		
2,0	6	5	8	2,0	1,0	5	1,2	23112.0020
2,0	9	5	8	2,0	1,0	5	1,6	23112.0021
2,1	6	5	8	2,0	1,0	5	1,2	23112.0022
2,1	9	5	8	2,0	1,0	5	1,5	23112.0023
2,5	6	5	8	2,0	1,0	5	1,1	23112.0024
2,5	9	5	8	2,0	1,0	5	1,4	23112.0025
3,0	8	6	9	2,5	1,0	6	1,9	23112.0030
3,0	12	6	9	2,5	1,0	6	2,6	23112.0031
3,0	16	6	9	2,5	1,0	6	3,2	23112.0032
3,1	8	6	9	2,5	1,0	6	1,9	23112.0033
3,1	12	6	9	2,5	1,0	6	2,5	23112.0034
3,1	16	6	9	2,5	1,0	6	3,2	23112.0035
3,5	8	7	10	2,5	1,0	7	2,4	23112.0036
3,5	12	7	10	2,5	1,0	7	3,4	23112.0037
3,5	16	7	10	2,5	1,0	7	4,3	23112.0038
4,0	8	7	10	2,5	1,0	7	2,3	23112.0040
4,0	12	7	10	2,5	1,0	7	3,1	23112.0041
4,0	16	7	10	2,5	1,0	7	3,9	23112.0042
4,1	8	8	11	2,5	1,0	8	3,0	23112.0043
4,1	12	8	11	2,5	1,0	8	4,2	23112.0044
4,1	16	8	11	2,5	1,0	8	5,3	23112.0045
4,5	8	8	11	2,5	1,0	8	2,9	23112.0046
4,5	12	8	11	2,5	1,0	8	3,9	23112.0047
4,5	16	8	11	2,5	1,0	8	5,0	23112.0048
5,0	8	8	11	2,5	1,0	8	1,8	23112.0050
5,0	12	8	11	2,5	1,0	8	3,6	23112.0051
5,0	16	8	11	2,5	1,0	8	4,5	23112.0052

d ₁ F7	l ₁	尺寸				r	定位孔 D H7 [mm]	 [g]	品號
		d ₂ n6 [mm]	d ₃	l ₂					
5,1	10	10	13	3,0	1,5	10	5,5	23112.0053	
5,1	16	10	13	3,0	1,5	10	8,2	23112.0054	
5,1	20	10	13	3,0	1,5	10	10,0	23112.0055	
5,5	10	10	13	3,0	1,5	10	5,3	23112.0056	
5,5	16	10	13	3,0	1,5	10	7,9	23112.0057	
5,5	20	10	13	3,0	1,5	10	9,6	23112.0058	
6,0	10	10	13	3,0	1,5	10	4,9	23112.0060	
6,0	16	10	13	3,0	1,5	10	7,3	23112.0061	
6,0	20	10	13	3,0	1,5	10	8,8	23112.0062	
6,1	10	12	15	3,0	1,5	12	7,7	23112.0063	
6,1	16	12	15	3,0	1,5	12	12,0	23112.0064	
6,1	20	12	15	3,0	1,5	12	14,0	23112.0065	
6,5	10	12	15	3,0	1,5	12	7,4	23112.0066	
6,5	16	12	15	3,0	1,5	12	11,0	23112.0067	
6,5	20	12	15	3,0	1,5	12	14,0	23112.0068	
7,0	10	12	15	3,0	1,5	12	7,0	23112.0070	
7,0	16	12	15	3,0	1,5	12	10,0	23112.0071	
7,0	20	12	15	3,0	1,5	12	13,0	23112.0072	
7,1	10	12	15	3,0	1,5	12	6,9	23112.0073	
7,1	16	12	15	3,0	1,5	12	10,0	23112.0074	
7,1	20	12	15	3,0	1,5	12	13,0	23112.0075	
7,5	10	12	15	3,0	1,5	12	6,5	23112.0076	
7,5	16	12	15	3,0	1,5	12	9,7	23112.0077	
7,5	20	12	15	3,0	1,5	12	12,0	23112.0078	
8,0	10	12	15	3,0	1,5	12	6,0	23112.0080	
8,0	16	12	15	3,0	1,5	12	9,0	23112.0081	
8,0	20	12	15	3,0	1,5	12	11,0	23112.0082	
8,1	12	15	18	3,0	2,0	15	13,0	23112.0083	
8,1	20	15	18	3,0	2,0	15	25,0	23112.0084	
8,1	25	15	18	3,0	2,0	15	26,0	23112.0085	
8,5	12	15	18	3,0	2,0	15	13,0	23112.0086	
8,5	20	15	18	3,0	2,0	15	20,0	23112.0087	
8,5	25	15	18	3,0	2,0	15	25,0	23112.0088	
9,0	12	15	18	3,0	2,0	15	12,0	23112.0090	
9,0	20	15	18	3,0	2,0	15	19,0	23112.0091	
9,0	25	15	18	3,0	2,0	15	23,0	23112.0092	
9,1	12	15	18	3,0	2,0	15	12,0	23112.0093	
9,1	20	15	18	3,0	2,0	15	19,0	23112.0094	
9,1	25	15	18	3,0	2,0	15	23,0	23112.0095	
9,5	12	15	18	3,0	2,0	15	11,0	23112.0096	
9,5	20	15	18	3,0	2,0	15	18,0	23112.0097	
9,5	25	15	18	3,0	2,0	15	22,0	23112.0098	
10,0	12	15	18	3,0	2,0	15	10,0	23112.0100	
10,0	20	15	18	3,0	2,0	15	17,0	23112.0101	
10,0	25	15	18	3,0	2,0	15	20,0	23112.0102	
10,1	12	18	22	4,0	2,0	18	19,0	23112.0103	
10,1	20	18	22	4,0	2,0	18	30,0	23112.0104	
10,1	25	18	22	4,0	2,0	18	37,0	23112.0105	
10,5	12	18	22	4,0	2,0	18	19,0	23112.0106	
10,5	20	18	22	4,0	2,0	18	29,0	23112.0107	
10,5	25	18	22	4,0	2,0	18	36,0	23112.0108	
11,0	12	18	22	4,0	2,0	18	18,0	23112.0110	
11,0	20	18	22	4,0	2,0	18	28,0	23112.0111	
11,0	25	18	22	4,0	2,0	18	34,0	23112.0112	
11,1	12	18	22	4,0	2,0	18	18,0	23112.0113	
11,1	20	18	22	4,0	2,0	18	28,0	23112.0114	
11,1	25	18	22	4,0	2,0	18	34,0	23112.0115	
11,5	12	18	22	4,0	2,0	18	17,0	23112.0116	
11,5	20	18	22	4,0	2,0	18	26,0	23112.0117	
11,5	25	18	22	4,0	2,0	18	33,0	23112.0118	
12,0	12	18	22	4,0	2,0	18	16,0	23112.0120	

d ₁ F7	l ₁	尺寸				r	定位孔 D H7 [mm]	 [g]	品號
		d ₂ n6 [mm]	d ₃	l ₂					
12,0	20	18	22	4,0	2,0	18	25,0	23112.0121	
12,0	25	18	22	4,0	2,0	18	31,0	23112.0122	
12,1	16	22	26	4,0	2,0	22	37,0	23112.0123	
12,1	28	22	26	4,0	2,0	22	62,0	23112.0124	
12,1	36	22	26	4,0	2,0	22	78,0	23112.0125	
12,5	16	22	26	4,0	2,0	22	36,0	23112.0126	
12,5	28	22	26	4,0	2,0	22	60,0	23112.0127	
12,5	36	22	26	4,0	2,0	22	76,0	23112.0128	
13,0	16	22	26	4,0	2,0	22	34,0	23112.0130	
13,0	28	22	26	4,0	2,0	22	58,0	23112.0131	
13,0	36	22	26	4,0	2,0	22	73,0	23112.0132	
14,0	16	22	26	4,0	2,0	22	32,0	23112.0140	
14,0	28	22	26	4,0	2,0	22	198,0	23112.0141	
14,0	36	22	26	4,0	2,0	22	67,0	23112.0142	
15,0	16	22	26	4,0	2,0	22	29,0	23112.0150	
15,0	28	22	26	4,0	2,0	22	48,0	23112.0151	
15,0	36	22	26	4,0	2,0	22	61,0	23112.0152	
16,0	16	26	30	4,0	2,0	26	45,0	23112.0160	
16,0	28	26	30	4,0	2,0	26	76,0	23112.0161	
16,0	36	26	30	4,0	2,0	26	97,0	23112.0162	
16,1	16	26	30	4,0	2,0	26	45,0	23112.0163	
16,1	28	26	30	4,0	2,0	26	76,0	23112.0164	
16,1	36	26	30	4,0	2,0	26	96,0	23112.0165	
16,5	16	26	30	4,0	2,0	26	44,0	23112.0166	
16,5	28	26	30	4,0	2,0	26	73,0	23112.0167	
16,5	36	26	30	4,0	2,0	26	93,0	23112.0168	
17,0	16	26	30	4,0	2,0	26	42,0	23112.0171	
17,0	28	26	30	4,0	2,0	26	70,0	23112.0172	
17,0	36	26	30	4,0	2,0	26	89,0	23112.0173	
18,0	16	26	30	4,0	2,0	26	39,0	23112.0181	
18,0	28	26	30	4,0	2,0	26	64,0	23112.0182	
18,0	36	26	30	4,0	2,0	26	82,0	23112.0183	
19,0	20	30	34	5,0	3,0	30	71,0	23112.0191	
19,0	36	30	34	5,0	3,0	30	125,0	23112.0192	
19,0	45	30	34	5,0	3,0	30	154,0	23112.0193	
20,0	20	30	34	5,0	3,0	30	67,0	23112.0201	
20,0	36	30	34	5,0	3,0	30	117,0	23112.0202	
20,0	45	30	34	5,0	3,0	30	143,0	23112.0203	
20,1	20	30	34	5,0	3,0	30	66,0	23112.0204	
20,1	36	30	34	5,0	3,0	30	115,0	23112.0205	
20,1	45	30	34	5,0	3,0	30	142,0	23112.0206	
22,0	20	30	34	5,0	3,0	30	56,0	23112.0221	
22,0	36	30	34	5,0	3,0	30	96,0	23112.0222	
22,0	45	30	34	5,0	3,0	30	120,0	23112.0223	
25,0	20	35	39	5,0	3,0	35	80,0	23112.0251	
25,0	36	35	39	5,0	3,0	35	138,0	23112.0252	
25,0	45	35	39	5,0	3,0	35	171,0	23112.0253	
30,0	25	42	46	5,0	3,0	42	139,0	23112.0301	
30,0	45	42	46	5,0	3,0	42	245,0	23112.0302	
30,0	56	42	46	5,0	3,0	42	303,0	23112.0303	

遵守

符合 RoHS

含鉛 - 相容除了例外 6a / 6b / 6c.

含有 >0.1% w/w 的 SVHC 物質

含鉛 - SVHC [REACH] 清單截至 2024 年 6 月 27 日

包含 65 號提案的物質



接觸鉛會導致癌症和生殖危害。接觸鎳會導致癌症。

<https://www.P65Warnings.ca.gov/>

不含衝突礦物

本產品不含來自剛果民主共和國或鄰近國家的任何被指定為“衝突礦物”的物質，例如鈹、錫、金或鎢。