

POS SOLUTIONS



POS SOLUTIONS

Halder offers specialised retail point of sale assortments that can be tailored to specific industries or that can offer a more general assortment to meet the customers needs.

These displays can be changed to meet the necessary retail space requirements.

The Halder sales team would be pleased to answer any questions you might have to help build an appropriate display to meet your needs.

POS SHELF “CONSTRUCTION”

1,60 m x 1,00 m



2,00 m x 1,00 m



2,40 m x 1,00 m



Description

This suggested listing includes the SIMPLEX classics for gardening and landscaping extended with an assortment of SIMPLEX sledge hammers, non-marring inserts, a targeted selection of non-rebound hammers and the new Halder entry-level soft-face hammer BASEPLEX.

See the file “Suggested Listing - Construction” for details of the product assortment.

POS SHELF “CONSTRUCTION SMALL”

basic product presentation

with product application pictures

with lighted header sign



Description

This option of the suggested listing “Construction” is a space-saving alternative that can be integrated in existing shelving units. Here the focus is on the SIMPLEX classics for gardening and landscaping.

See the file “Suggested Listing - Construction Small” for details of the product assortment.

POS SHELF “CONSTRUCTION + FORESTRY”

1,60 m x 1,00 m



2,00 m x 1,00 m



2,40 m x 1,00 m



Description

This is a variant of the suggested listing “Construction“. The SIMPLEX splitting Maul, the SIMPLEX splitting Axe, as well as the Twisted splitting wedge are integrated here.

See the file “Suggested Listing - Construction + Forestry“ for details of the product assortment.

POS SHELF “CONTRACTORS”

1,60 m x 1,00 m



2,00 m x 1,00 m



2,40 m x 1,00 m



Description

This suggested listing offers a broad assortment of soft-face mallets for all conceivable tasks. Including the SIMPLEX with alloy housing (ideal for carpentry tasks), the SECURAL (ideal for flooring) and the MAXXCRAFT, the rebound-dampening locksmith's hammer with 25% more impact power.

See the file “Suggested Listing - Contractors” for details of the product assortment.

POS SHELF “INDUSTRY”

1,60 m x 1,00 m



2,00 m x 1,00 m



2,40 m x 1,00 m



Description

This recommendation includes a broad selection of the SUPERCRAFT non-rebound mallets with different types of handles (wood, steel, and 3-component). Likewise the SIMPLEX with soft metal inserts and copper inserts, as well as the FERROPLEX combi hammers are included.

See the file “Suggested Listing - Industry” for details of the product assortment.

POS SHELF “GONDOLA”



Description

The base rack can be stocked on both sides, regardless of the shelf height selected, thus it can also be placed as a gondola solution in the middle of the sales area.

CROSSBAR FOR TOOL TRADERS



Description

This crossbar solution can be integrated in existing shelving units. The recommendation contains the most important products for tool traders.

See the “Suggested Listing – Crossbar for Tool Traders“ for details of the product assortment.

Product mix can be customised to meet needs.

SHELF COMPONENTS



Lighted sign frame 400 mm

The lighted sign frame is offered with or without light.

Without light	Art. no. 3000.1007
With light	Art. no. 3000.1009
Top sign	Art. no. 3000.1010



Lighted sign frame 200 mm

Without light	Art. no. 3000.1006
With light	Art. no. 3000.1008
Top sign small	Art. no. 3000.1011



Advertising sign

Blank metal panel	Art. no. 3000.1012
Application picture sign (magnetic)	Art. no. 3000.1064



SHELF COMPONENTS



Art. no. 3000.1000
POS base rack

Art. no. 3000.1002
Back wall for base rack

SHELF COMPONENTS



Art. no. 3000.1001 Base rack extension

Set consisting of right and left extension.
For extending the base rack from:
1.60 m to 2.00 m (1 set) or
1.60 m to 2.40 m (2 sets)



Crossbar

Is used for hooking in the holders or the boxes. Also suitable for existing standard shelving units.

Crossbar B 1000 mm

Art. 3000.1013

Crossbar B 1250 mm

Art. 3000.1028

Crossbar B 1330 mm


Art. 3000.1029

SHELF COMPONENTS




Art. no. 3000.1004
Back wall extension
800 x 960 x 3 mm

To extend the back wall from 1.60 m to 2.40 m



Art. no. 3000.1003
Back wall extension
400 x 960 x 3 mm

To extend the back wall from 1.60 m to 2.00 m



Art. no. 3000.1005
Back wall connector width 1000mm


To connect the basic back wall with the back wall extension

PRODUCT HANGERS



Art. no. 3000.1016
Hanger small (ø 25-50 mm)

For all SIMPLEX, SUPERCRAFT and BASEPLEX mallets,
diameters 25-50 mm.



PRODUCT HANGERS



Art. no. 3000.1019

Hanger medium (ø 40-70 mm)

For all SIMPLEX, SUPERCRAFT and BASEPLEX mallets, diameters 40-70 mm.

Examples:




PRODUCT HANGERS



Art. no. 3000.1018
Hanger large (ø 50-80 mm)

For all SIMPLEX, SUPERCRAFT and BASEPLEX mallets,
diameters 50-80 mm.



PRODUCT HANGERS



Art. no. 3000.1017 MAXXCRAFT Hanger

For the following MAXXCRAFT sizes:

- 1 x 1000 g
- 2 x 800 g
- 2 x 500 g
- 2 x 300 g



Art. no. 3000.1021 SUPERCRAFT / SECURAL Hanger mixed

For the following suggested listing:

- 2 x SECURAL
- 1 x SUPERCRAFT \varnothing 60
- 1 x SUPERCRAFT \varnothing 50
- 1 x SUPERCRAFT \varnothing 40



Art. no. 3000.1020 FERROPLEX / SECURAL Hanger mixed

For the following suggested listing:

- 4 x SECURAL
- 2 x FERROPLEX \varnothing 35
- 2 x FERROPLEX \varnothing 30

PRODUCT HANGERS



Art. no. 3000.1014
Splitting Wedge Hanger

For article 3556.260 Halder twisted splitting wedge.



Art. no. 3000.1015
Long Handle Holder

For safe setup of the sledge hammers and forestry products.



Art. no. 3000.1022
Brochure Holder

For optional brochures.


BOXES



Art. no. 3000.1024 Small Box

For clearly organised presentation of the soft-face mallet inserts. Dividers included.

BOXES



Art. no. 3000.1023

Large Box

For clearly organised presentation of the sledge hammers, forestry products, as well as the soft-face mallet inserts and replacement handles. Dividers included.

Suitable product description signs are provided in German for all hangers and shelves.

HANGER SIGNS

Examples:

SIMPLEX

Inserts:

TPE-soft
Hardness: ●○○○○

- for very delicate material (non-damaging)

TPE-mid
Hardness: ●●○○○

- for delicate material

non-marring

non-marring

Art.-Nr. 3000.2206

⌘ SUPERCRAFT

Inserts:

Nylon
Hardness: ●●●●○

- very wear-resistant
- no chipping or cracking
- noise dampening
- very high impact

non-rebound

Art.-Nr. 3000.2212

FERROPLEX

Inserts:

Nylon
Hardness: ●●●●○

- very wear-resistant
- no chipping or cracking
- noise dampening

Steel
Hardness: ●●●●●

- high-grade tempered steel face

⌘ SECURAL

Inserts:

Polyurethane
Hardness: ●●●○○

- rectangular face
- noise-dampening, cushioning
- wear-resistant

non-rebound

Art.-Nr. 3000.2214

MAXXCRAFT

Steel Head:

- 25% more impact power
- 70% less vibration
- gentle on the joints
- reduces work fatigue
- extra large overstrike protector


reduced rebound



Art.-Nr. 3000.2211

Each merchandise hanger is equipped with an individual sign. On the sign the hardness, as well as other characteristics of the inserts of the displayed mallets are explained; this makes it easier for the customer to select the right product.

BOX SIGNS



Art. no. 3000.1065

Signboard for small box

This signboard shows the 8 available SIMPLEX inserts and their hardness.

LABELLING

Art. no. 3000.1066 Signboard for large box "Standard"

<p>SIMPLEX Soft face mallet/sledge hammer</p> <ul style="list-style-type: none"> • all parts are replaceable • 3 different housing materials • 2 different handle materials • 8 different insert materials • available sizes from ø 30 to 140 mm 	<p>⇨ SUPERCRAFT Soft face mallet/sledge hammer</p> <ul style="list-style-type: none"> • easy on joints, noise-dampening • full transmission of power upon impact • extremely durable • inserts replaceable • available sizes from 245g to 10kg 	<p>BASEPLEX Soft face mallet</p> <ul style="list-style-type: none"> • for industry, home, construction • inserts: nylon and acetate plastic • extra large overstrike protector • available sizes from ø 25 to 50 mm 
--	---	--

Art. no. 3000.1067 Signboard for large box "Forestry"

<p>⇨ SUPERCRAFT Soft face mallet/sledge hammer</p> <ul style="list-style-type: none"> • easy on joints, noise-dampening • full transmission of power upon impact • extremely durable • inserts replaceable • available sizes from 245g to 10kg 	<p>SIMPLEX Soft face mallet/sledge hammer</p> <ul style="list-style-type: none"> • all parts are replaceable • 3 different housing materials • 2 different handle materials • 8 different insert materials • available sizes from ø 30 to 140 mm 	<p>SIMPLEX Splitting maul/axe, twisted splitting wedge</p> <ul style="list-style-type: none"> • all parts are replaceable • for safe driving of steel wedges • 2 in 1: Splitting tool + soft face mallet • efficient splitting • unique „twisted“ design 
--	---	--

Art. no. 3000.1068 Signboard for large box "Photos"



For the labelling of the large box there are 3 versions available that are used depending on the assortment and shelf height.

COUNTER DISPLAY



Art. no. 3000.1100 Counter Display

For all Halder soft-face mallets from
ø 25 to ø 50 mm.



Supercraft
Front



Supercraft
Back



Mixed I



Mixed II

Signboard Counter Display

Supercraft Front

Art. 3000.1086

Supercraft Back

Art. 3000.1087

Mixed I

Art. 3000.1088

Mixed II

Art. 3000.1089

Baseplex Front

Art. 3000.1090

Baseplex Back

Art. 3000.1091

Simplex Front

Art. 3000.1095

Simplex Back


Art. 3000.1096



Baseplex
Front



Baseplex
Back



Simplex
Front



Simplex
Back

POUNDING STATION



Art. no. 3000s001

Pounding station - soft-face mallet

For testing the Halder hammers MAXXCRAFT, SUPERCRAFT and SECURAL in comparison with a standard locksmith's hammer. (The 3 Halder hammers, as well as protective glasses are included.)

